



SPRAYER SPECIFICATIONS

Use airless equipment with

- A flow rate of 1.5 to 2GPM**
- 2500 to 3000 PSI**
- Use tip size 629 (12" fan pattern and .029 orifice size) to 645 (12" fan pattern and .045 orifice size).**

If the airless equipment has a machine filter in addition to the intake rock screen, use a 40-mesh filter or temporarily remove the machine filter cartridge altogether while applying Maximum-Stretch.

For professional high production application techniques consult Ames Tech Services (1-888-345-0809) for larger equipment recommendations.